


# The Dentastic Five. Your everyday heroes.



They've come to save your restoration removal routines.

The separation and removal of dental crowns and fillings count among the routine jobs at any dental practice. To suit the properties of the different materials, numerous instruments are available for these applications. This can at times lead to uncertainty when it comes to choosing the right instrument. This is now a thing of the past! Komet's Dentastic Five have come to the rescue: a set for a fast and effective workflow during separation and removal – ready for use on any established restoration material.

- Handy specialists for any material.
- Practical trial set.
- Suitable for processing in a laser marked stainless steel bur block.



**Set K-4687ST**  
Dentastic Five in a sterilisable stainless steel bur block

## The gentle one



●● **H32.314.012**  
Amalgam remover

## The specialist



○● **4ZRS.314.016**  
Crown-cutter "Jack" for all-ceramic restorations

## The all-rounder



○● **H4MCL.314.012**  
Crown-cutter for PFM crowns and metal frames

## NEW: THE ANGULAR ONE

- Outstanding removal capacity thanks to a structured blank and an active tip provided with larger chip spaces.
- The 4COMP is distinguished by its consistently high removal capacity.
- The durability of the 4COMP is clearly superior to that of other instruments, in particular tungsten carbide burs.



●● **4COMP.314.012**  
Composite remover




## NEW: THE SNAPPY ONE

- Cuts through hard non-precious metal crowns in record time.
- Snappy – thanks to special cross-cut tooting.
- Powerful and efficient, yet particularly durable.



●● **H4NP.314.016**  
Crown-cutter non-precious metal alloys



**TIP:** Scan the below code to find out more about the Dentastic Five.



Scan it!